

42BA
chiavi combinate a forchetta e poligonale piegata antiscintilla


		art.	 mm	A mm	Ø mm	L mm	S1 mm	S2 mm	 g
	000420806	42BA 6	6x6	12,0	12,0	105	6,0	8,0	38
	000420807	42BA 7	7x7	18,5	12,0	105	6,5	7,5	41
	000420808	42BA 8	8x8	20,0	13,5	120	6,5	7,5	48
	000420809	42BA 9	9x9	21,0	15,5	120	7,0	8,0	54
	000420810	42BA 10	10x10	23,0	15,5	135	7,0	9,0	68
	000420811	42BA 11	11x11	26,0	18,0	135	7,5	9,5	75
	000420812	42BA 12	12x12	27,0	19,0	150	7,5	9,5	80
	000420813	42BA 13	13x13	31,0	21,5	150	7,5	10,0	101
	000420814	42BA 14	14x14	31,0	22,0	175	8,0	11,0	123
	000420815	42BA 15	15x15	32,5	23,5	175	8,0	10,5	123
	000420816	42BA 16	16x16	35,5	25,0	195	8,0	11,5	151
	000420817	42BA 17	17x17	37,0	26,5	200	9,0	12,5	177
	000420818	42BA 18	18x18	39,5	32,0	215	7,6	11,0	210
	000420819	42BA 19	19x19	41,5	30,0	220	9,8	13,0	208
	000420820	42BA 20	20x20	43,5	31,5	230	10,0	13,8	255
	000420821	42BA 21	21x21	44,5	33,0	240	10,0	14,5	306
	000420822	42BA 22	22x22	47,0	34,0	250	10,5	15,0	304
	000420824	42BA 24	24x24	50,0	38,0	268	10,8	16,0	376
	000420826	42BA 26	26x26	56	42,0	290	12,5	17,0	420
	000420827	42BA 27	27x27	56,5	42,0	290	12,0	18,5	490
	000420828	42BA 28	28x28	56,5	42,0	290	11,4	18,5	410
	000420830	42BA 30	30x30	56,5	45,0	313	13,0	18,5	696
	000420832	42BA 32	32x32	66,5	50,0	333	13,5	22,5	778
	000420834	42BA 34	34x34	71,5	55,0	360	16,0	21,0	850
	000420835	42BA 35	35x35	72,0	55,0	360	15,0	21,0	890
	000420836	42BA 36	36x36	77,0	58,0	355	15,0	23,5	1094
	000420838	42BA 38	38x38	78,5	58,0	430	15,0	23,5	1157
	000420841	42BA 41	41x41	84,5	63,0	430	16,0	23,5	1305
	000420846	42BA 46	46x46	92,0	69,0	480	17,0	24,0	1589
	000420850	42BA 50	50x50	100,0	74,0	520	18,0	25,0	2100
	000420855	42BA 55	55x55	114,0	83,0	560	19,0	26,0	2700
	000420860	42BA 60	60x60	119,0	89,0	580	21,0	27,0	3550
★	000420865	42BA 65	65x65	125,0	95,0	595	21,0	27,0	3680
★	000420870	42BA 70	70x70	142,0	112,0	630	24,0	29,0	4770



Questo utensile è in lega beryllio-cobalto (Cu-Be) e non deve essere usato in modo
 che produca scintille o altre forme di esposizione elettromagnetica o termica.
 I componenti e i materiali non devono essere usati per applicazioni a ultrasuoni.
 This instrument is made of beryllium-copper alloy (Cu-Be) and should not be used in
 applications that produce sparks or other forms of electromagnetic or thermal exposure.
 The components and materials should not be used for ultrasonic applications.
 This instrument is made of beryllium-copper alloy (Cu-Be) and should not be used in
 applications that produce sparks or other forms of electromagnetic or thermal exposure.
 The components and materials should not be used for ultrasonic applications.

